

Contents

	page
Introduction.....	1
Nomenclature.....	7
Literature (data sources).....	9
Data sheets:	
TTStE 32.....	15
StE 460.....	18
StE 460 coldformed.....	34
StE 460 rolled skin.....	37
WStE 460.....	41
StE 590 (HT 60).....	45
StE 590 (A302B).....	48
StE 690.....	54
StE 690 prestrained.....	61
StE 690 rolled skin.....	65
17 MnCrMo 3 3 (N-A-Xtra 70).....	72
17 MnCrMo 3 3 (N-A-Xtra 70) $\epsilon_m \neq 0$	79
17 MnCrMo 3 3 (N-A-Xtra 70) elevated temperature.....	86
11 NiMnCrMo 5 5 (HSB 77 V).....	89
StE 790 (HT 80, HY 80, AISI 1080).....	93
HY 130.....	114
BHW 25.....	117
17 MnNiMo 5 3 4 (BHW 38).....	120
17 MnNiMo 5 3 4 (BHW 38) elevated temperature.....	123
15 MnMoNiV 5 3.....	126
15 MnMoNiV 5 3 elevated temperature.....	129
17 MnMoV 6 4 (WB 35).....	132
17 MnMoV 6 4 (WB 35) elevated temperature.....	135
2 MnCr 7 8.....	138
2 MnCr 7 8 low temperature.....	141
4 MnMo 7.....	144

4 MnMo 7 low temperature.....	147
8 Mn 6.....	150
12 MnMo 5 (SPV 50).....	156
14 Mn 5 (Van-80).....	168
14 Mn 5 (Van-80) prestrained.....	171
19 Mn 5 elevated temperature.....	174
20 Mn 3 (RQC 100).....	177
20 Mn 3 (RQC 100) prestrained.....	180
22 MnCrNi 3 (AISI 8620H).....	183
22 MnCrNi 3 (AISI 8620H) carburized.....	186
23 Mn 4 (AOS 1122 B).....	189
25 Mn 3 (A36).....	192
25 Mn 4 (A-516 Gr 70, AOS 1122 A).....	195
28 MnCu 6 (Man-Ten).....	214
28 MnCu 6 (Man-Ten) prestrained.....	217
30 MnCr 5 (C30MB).....	220
41 MnCr 3 4 (41CrM4B).....	223
49 MnVS 3.....	226
49 MnVS 3 $\epsilon_m \neq 0$	229
80 Mn 4 (ASTM A1).....	235
10 CrMo 9 10 (SCMV4).....	238
10 CrMo 9 10 elevated temperature.....	247
12 CrMo 8 (2 1/4 Cr 1 Mo).....	295
13 CrMo 4 4.....	298
13 CrMo 4 4 elevated temperature.....	316
13 CrMo 4 4 rough surface.....	349
14 CrMo 9 10 elevated temperature.....	355
16 CrMo 5 4 (SCMV3).....	367
16 CrMo 5 4 (SCMV3) elevated temperature.....	376
28 CrMoNiV 4 9.....	424
28 CrMoNiV 4 9 elevated temperature.....	427

30 CrNiMo 8.....	430
34 CrNiMo 6.....	452
30 CrMo 2 (AISI 4130).....	455
37 CrMo 2 (SCM435).....	461
40 CrMo 4.....	464
42 CrMo 4.....	467
42 CrMo 4 $\varepsilon_m \neq 0$	494
55 Cr 3.....	500
100 Cr 6 (AISI 52100).....	506
14 MoV 6 3.....	509
14 MoV 6 3 elevated temperature.....	512
15 Mo 3.....	518
15 Mo 3 elevated temperature.....	524
NiCrMo 10 (EN 25).....	527
4 NiCrMn 4 (IN 787).....	533
16 NiCrMo 3 2 (A 514).....	536
23 NiCr 4 (USST-1).....	539
23 NiCr 4 (USST-1) prestrained.....	542
28 NiCrMo 7 4.....	545
40 NiCrMo 7 (AISI 4340).....	548
43 NiCr 7 9 (SAE 4340).....	554
43 NiCr 7 9 (SAE 4340) prestrained.....	560
CuNiMo.....	563
CuNiMo elevated temperature.....	566